



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 60A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Watertight



By Bryant
Catalog # 460P12W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 60A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Orange, Watertight

Features

- Industrial Grade
- Male Plug
- 60A 125/250V
- 3-Pole 4-Wire Grounding
- Screw Terminals

Application

High Ampacity Connections

General

Catalog Number	460P12W
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Plugs
UPC	781786251441

Dimensions

Display Size

Standard Sized

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none"> • 125 VAC • 250 VAC
Voltage Rating Description	125 VAC;250 VAC
Wattage	15000

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 460P12W](#)