



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 63A 3-Phase Delta 250V AC, Screw Terminals, Watertight

By Bryant  
Catalog # 463R6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 63A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Screw Terminals, Red, Watertight

## Features

- Industrial Grade
- Female Receptacle
- 63A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- Screw Terminals

## Application

High Ampacity Connections

## General

Catalog Number	463R6W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786251557

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	63 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	63 A
Current Rating	63 A
Phase	Single Phase
Voltage Rating	380-415 V
Voltage Rating Description	380-415V
Wattage	26145

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets

[Specifications - 463R6W](#)