



Locking Devices, Locking Devices, Marine Grade, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Yellow

By Bryant
Catalog # 4700DRCR



Locking Devices, Marine Grade, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Corrosion-Resistant, Yellow

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	4700DRCR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Duplex Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Type	Receptacle
UPC	781786002043

Dimensions

Dimensions	3.28 in x 1.70 in x 0.93 in
Display Size	Standard Sized Product
Height	0.93 in

Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L5-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-7 Catalog Page](#)
[Catalog Page - BRY J-3 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 4700DRCR](#)