



# Locking Devices, Locking Devices, Isolated Ground Industrial, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5- 15R, Screw Terminal, Orange

By Bryant  
Catalog # 4700DRIG



Locking Devices, Isolated Ground Industrial, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5- 15R, Screw Terminal, Orange

## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

## General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	4700DRIG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Duplex Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Locking
Style	Isolated Ground
Type	Duplex Receptacle
UPC	781786002067

## Dimensions

Dimensions	3.28 in x 1.70 in x 0.93 in
Display Size	Standard Sized Product
Height	0.93 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY H-7 Catalog Page](#)
- [Catalog Page - BRY D-7 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-4700DRIG-SPEC-EN | REV 6/2024