



# Locking Devices, Locking Devices, Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5- 15R, Screw Terminal, Black

By Bryant  
Catalog # 4710

Locking Devices, Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-  
Wire Grounding, L5-15R, Screw Terminal, Black



## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

## General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	4710
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Nylon Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786174016

## Dimensions

Dimensions	3.28 in x 1.41 in x 1.01 in
Display Size	Standard Sized Product
Height	1.01 in
Length	3.28 in
Width	1.41 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4800

## Product Assets

[Catalog Page - BRY Q-18 Catalog Page](#)  
[Catalog Page - BRY H-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-4710-SPEC-EN | REV 6/2024