



Locking Devices, Locking Devices, Industrial, Panel Mount Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black

By Bryant
Catalog # 4713BRY

Locking Devices, Industrial, Panel Mount Receptacle, 15A 125V,
2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black, 1.75"
Mounting Hole Center



Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Panel Mount Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Panel Mount
Type	Receptacle
UPC	781786616134

Dimensions

Dimensions	2.38 in x 1.41 in x 1.09 in
Display Size	Standard Sized Product
Height	1.09 in
Length	2.38 in
Width	1.41 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L5-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-4713BRY-SPEC-EN | REV 5/2023