



# Locking Devices, Locking Devices, Industrial, Male Plug, 15A 125V, 2- Pole 3-Wire Grounding, L5-15P, Screw Terminal, Armored

By Bryant  
Catalog # 4726BRY



Locking Devices, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire  
Grounding, L5-15P, Screw Terminal, Armored

## Application

Extra Heavy Duty Industrial

## General

Color	All Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Regular Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Two-Piece Cord Clamp
Type	Plugs
UPC	781786656574

## Dimensions

Dimensions	1.53 in x 1.53 in x 2.00 in
Display Size	Standard Sized
Height	2.00 in
Length	1.53 in
Width	1.53 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Nema Rating	L5-15R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-6 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-4726BRY-SPEC-EN | REV 5/2023