



# Locking Devices, Locking Devices, Industrial, Flush Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Brown

By Bryant  
Catalog # 4760



Locking Devices, Industrial, Flush Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Black

## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	4760
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Nylon Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786623323

## Dimensions

Dimensions	3.28 in x 1.41 in x 1.01 in
Display Size	Standard Sized Product
Height	1.01 in
Length	3.28 in

Width 1.41 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277V AC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L7-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4800

## Product Assets

[Catalog Page - BRY Q-18 Catalog Page](#)  
[Catalog Page - BRY H-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 4760](#)