



Locking Devices, Locking Devices, Industrial, Flush Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Black, With Cover

By Bryant
Catalog # 4761



Locking Devices, Industrial, Flush Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Black, Mounted on 4" Round Metal Box

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	4761
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Nylon Single Receptacle-Mounted on 4" Round Metal Box
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Box Mounted
Type	Receptacle
UPC	781786623330

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277V AC
Wattage	

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L7-15R
-------------	--------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - BRY H-7 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-4761-SPEC-EN | REV 6/2024