



# Locking Devices, Locking Devices, Industrial, Male Plug, 15A 277V AC, 2-Pole3-Wire Grounding, L7-15P, Screw Terminal, Black and White

By Bryant  
Catalog # 4770NP



Locking Devices, Industrial, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Black and White

## Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## Application

Extra Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786010307

## Dimensions

Dimensions	1.53 in x 1.53 in x 2.18 in
Display Size	Standard Sized
Height	2.18 in
Length	1.53 in
Width	1.53 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277 VAC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Nema Rating	L7-15P
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-6 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-4770NP-SPEC-EN | REV 4/2023