



Switches and Lighting Controls, Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 15A 120/277V AC, Back and Side Wired, Ivory

By Bryant
Catalog # 4801BI



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Single Pole, 15A 120/277V AC,
Back and Side Wired, Ivory

Application

Back and Side Wired

General

Color	Ivory
Series	Heavy Duty
Style	Single Pole
Type	Toggle
UPC	781786715387

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Heavy Duty Specification
Grade Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-4801BI-SPEC-EN | REV 5/2023