



Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 15A 120/277V AC, Back and Side Wired Nylon Key Guide, Packed with Key

By Bryant
Catalog # [4801L](#)

Switches and Lighting Controls, Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 15A 120/277V AC, Back and Side Wired, Black Nylon Key Guide, Packed with Key



Application

Back and Side Wired

General

Color	Black
Series	Extra Heavy Duty
Style	Single Pole
Type	Locking
UPC	781786623521

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Healthcare Solutions](#)

Related Products

[4901RKL - Security Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired Key Guide, Packed with Key](#)
[4901L - Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired Key Guide, Packed with Key](#)
[4804L - Locking Industrial Grade, Toggle Switches, General Purpose AC, Four Way, 15A 120/277V AC, Back and Side Wired Nylon Key Guide, Packed with Key](#)
[SS22RKLM - Wallplates and Boxes, Metallic Plates, 2- Gang, 1\) Security Opening, Standard Size, Stainless Steel](#)
[P1 - Wallplate, Toggle, 1-Gang, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-4801L-SPEC-EN | REV 5/2023