



Industrial Grade, Toggle Switches, General Purpose AC, Momentary Single Pole-Double Throw Center Off, 15A 120/277V AC, Back and Side Wired

By Bryant
Catalog # 4821GRY

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Momentary Single Pole-Double
Throw Center Off, 15A 120/277V AC, Back and Side Wired,
Gray



Application

Back and Side Wired

General

Color	Gray
Series	Extra Heavy Duty
Style	Single Pole Double Throw
Type	Toggle
UPC	781786623750

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY E-3 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-4821GRY-SPEC-EN | REV 5/2024