



# Industrial Grade, Toggle Switches, General Purpose AC, Double Pole- Double Throw Center Off, 15A 120/277V AC, Back and Side Wired

By Bryant  
Catalog # [4825I](#)

Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, General Purpose AC, Double Pole-Double Throw  
Center Off, 15A 120/277V AC, Back and Side Wired, Ivory



## Application

Back and Side Wired

## General

Color	Ivory
Series	Extra Heavy Duty
Style	Double Pole Double Throw
Type	Toggle
UPC	781786657403

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY E-3 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRY-4825I-SPEC-EN | REV 5/2024