



# Switches and Lighting Controls, Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired, Gray

By Bryant  
Catalog # 4901BGRY



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, General Purpose AC, Single Pole, 20A 120/277V AC,  
Back and Side Wired, Gray

## Application

Back and Side Wired

## General

Color	Gray
Series	Heavy Duty
Style	Single Pole
Type	Toggle
UPC	781786715271

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant E-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Heavy Duty Specification  
Grade Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-4901BGRY-SPEC-EN | REV 5/2023