



Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired Key Guide, Packed with Key

By Bryant
Catalog # [4901L](#)

Switches and Lighting Controls, Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired, Black Key Guide, Packed with Key



Application

Back and Side Wired

General

Color	Black
EU RoHS Indicator	No
Series	Extra Heavy Duty
Style	Single Pole
Type	Locking
UPC	781786623873

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalog Page - BRY E-3 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Healthcare Solutions](#)
[Literature - General Literature - BRYANT® Wiring Devices](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-4901L-SPEC-EN | REV 5/2024