



# Locking Industrial Grade, Toggle Switches, General Purpose AC, Four Way, 20A 120/277V AC, Back and Side Wired Key Guide, Packed with Key

By Bryant  
Catalog # [4904L](#)

Switches and Lighting Controls, Locking Industrial Grade, Toggle Switches, General Purpose AC, Four Way, 20A 120/277V AC, Back and Side Wired, Black Key Guide, Packed with Key



## Application

Back and Side Wired

## General

Color	Black
Series	Extra Heavy Duty
Style	Four Way
Type	Locking
UPC	781786624047

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant E-3 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Healthcare Solutions](#)  
[Literature - General Literature - BRYANT® Wiring Devices](#)

## Related Products

[SS12RKL - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Security Opening, Standard Size, Stainless Steel](#)  
[4801L - Locking Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 15A 120/277V AC, Back and Side Wired Nylon Key Guide, Packed with Key](#)  
[SS22RKLM - Wallplates and Boxes, Metallic Plates, 2- Gang, 1\) Security Opening, Standard Size, Stainless Steel](#)  
[4904RKL - Security Locking Industrial Grade, Toggle Switches, General Purpose AC, Four Way, 20A 120/277V AC, Back and Side Wired, Chrome Lock](#)  
[4803L - Locking Industrial Grade, Toggle Switches, General Purpose AC, Three Way, 15A 120/277V AC, Back and Side Wired Nylon Key Guide, Packed with Key](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-4904L-SPEC-EN | REV 5/2023