



Industrial Grade, Toggle Switches, General Purpose AC, Momentary Single Pole-Double Throw Center Off, 20A 120/277V AC Back and Side Wired

By Bryant
Catalog # 4921



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Momentary Single Pole-Double
Throw Center Off, 20A 120/277V AC, Brown Back and Side
Wired, Brown

Application

Back and Side Wired

General

Color	Brown
Series	Extra Heavy Duty
Style	Single Pole Double Throw
Type	Toggle
UPC	781786624061

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-4921-SPEC-EN | REV 5/2023