



Switches and Lighting Controls, Industrial Grade, Push Button, General Purpose AC, Three Way, 15A 120/277V AC, Side Wired Only, Brown

By Bryant
Catalog # [4983](#)

Switches and Lighting Controls, Industrial Grade, Push Button,
General Purpose AC, Three Way, 15A 120/277V AC, Side Wired
Only, Brown



General

Color	Brown
Series	General Purpose
Style	Three Way
UPC	781786498303

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [4981 - Switches and Lighting Controls, Industrial Grade, Push Button, General Purpose AC, Single Pole, 15A 120/277V AC, Side Wired Only, Brown](#)
- [4984 - Switches and Lighting Controls, Industrial Grade, Push Button, General Purpose AC, Four Way, 15A 120/277V AC, Side Wired Only, Brown](#)
- [4982 - Switches and Lighting Controls, Industrial Grade, Push Button, General Purpose AC, Double Pole, 15A 120/277V AC, Side Wired Only, Brown](#)
- [1795WP - Wallplates and Boxes, Weatherproof Covers, 1-Gang, For PressSwitch, Standard Size, Silicone Rubber](#)
- [4998PLR - Push Button Switch, Three Way, 20A 120/277V AC, Pilot Red](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-4983-SPEC-EN | REV 5/2023