



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 100A 3-Phase Wye 120/208V AC, Watertight

By Bryant
Catalog # 5100R9W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 100A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Screw Terminals, Blue, Watertight

Features

- Industrial Grade
- Female Receptacle
- 100A 3-Phase Wye 120/208V AC
- 4- Pole 5-Wire Grounding
- Screw Terminals

Application

High Ampacity Connections

General

Catalog Number	5100R9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786251649

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 V
Voltage Rating Description	3 Phase Y 120/208V
Wattage	20800

Conductor Related

Number Of Wires	5-Wire
Wire Size	#3 AWG to #1/0 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance	CM
Status	

Product Assets

[Specifications - 5100R9W](#)