



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 125A 380/415V, Screw Terminals, Watertight



By Bryant  
Catalog # [5125C6W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 125A 380/415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

## Features

- Industrial Grade
- Female Connector Body
- 125A 380/415V
- 4-Pole 5-Wire Grounding
- Screw Terminals

## Application

High Ampacity Connections

## General

|                              |   |
|------------------------------|---|
| Catalog Number               | 5125C6W   |
| Color                        | Red   |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Watertight  |
| Insulation                   | Insulated Body  |
| Item Type                    | Watertight  |
| Material                     | Composite   |
| Material - Mounting Hardware | Cord Mounted  |
| Number Of Poles              | 4-Pole  |
| OEM Brand Name               | Hubbell Bryant  |
| Series                       | Watertight - IP67   |
| Temperature Rating           | Maximum Continuous: 75° C;<br>Minimum Continuous: -40° C<br>w/o impact, -25° with impact. |

|      |              |
|------|--------------|
| Type | Connector    |
| UPC  | 781786251663 |

## Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

## Electrical Ratings

|                            |                          |
|----------------------------|--------------------------|
| Amperage Rating            | 125 A                    |
| Connectivity               | Pressure Terminal Screws |
| Current / Amperage Rating  | 125 A                    |
| Current Rating             | 125 A                    |
| Voltage Rating             | 200/346 V 240/415 V      |
| Voltage Rating Description | 200/346V 240/415V        |

## Conductor Related

|                      |                    |
|----------------------|--------------------|
| Conductor Range      | #3 AWG to #1/0 AWG |
| Number Of Wires      | 5-Wire             |
| Number of Conductors | 5-Wire Grounding   |

## Certifications And Compliance

|             |          |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

## Product Assets

[Specifications - 5125C6W](#)