



Straight Blade Devices, HI-VIS, Commercial Grade, Female Connector, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Hi-Visibility Green

By Bryant
Catalog # 5159HVG



Straight Blade Devices, HI-VIS, Commercial Grade, Female Connector, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Single Pack, Hi-Visibility Green

Application

Heavy Duty

General

Color	Hi-Viz Green
Cord Range	0.245"-0.655"
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Female Connector
Material	Thermoplastic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786515932

Dimensions

Display Size	Standard Sized Product
Weight	0.1 lb

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5159HVG-SPEC-EN | REV 5/2023