



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 16A 380/415V, 4-Pole 5-Wire Grounding, Screw Terminals, Splash Proof



By Bryant  
Catalog # 516P6S

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 16A 380/415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Splash Proof

## Features

- Industrial Grade
- Male Plug
- 16A 380/415V
- 4-Pole 5-Wire Grounding
- Screw Terminals

## Application

High Ampacity Connections

## General

Catalog Number	516P6S
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Splash Proof
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Splashproof - IP44
Type	Plugs
UPC	781786252301

## Dimensions

Display Size Standard Sized

## Electrical Ratings

Amperage Rating	16 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	16 A
Current Rating	16 A
Phase	Multi Phase
Voltage Rating	200/346 V 240/415 V
Voltage Rating Description	200/346 V 240/415 V
Wattage	6640

## Conductor Related

Cord Type	All Portable
Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Nema Rating Non-NEMA

## Product Assets

[Specifications - 516P6S](#)



A Hubbell brand