



## Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 16A 380/415V, Screw Terminals, Splash Proof

By Bryant  
Catalog # 516R6S



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 16A 380/415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Splash Proof

### Features

- Industrial Grade
- Female Receptacle
- 16A 380/415V
- 4-Pole 5-Wire Grounding
- Screw Terminals

### Application

High Ampacity Connections

### General

Catalog Number	516R6S
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Splash Proof
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Splashproof - IP44
Type	Receptacle
UPC	781786252318

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Amperage Rating	16 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	16 A
Current Rating	16 A
Phase	Three Phase
Voltage Rating	200/346 V 240/415 V
Voltage Rating Description	200/346V 240/415V
Wattage	6640

### Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

### Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

### Product Assets

[Specifications - 516R6S](#)