



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Connector Body, 20A 3-Phase Wye 120/208V AC, 4- Pole 5-Wire Grounding, Watertight



By Bryant  
Catalog # 520C9W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 3-Phase Wye 120/208V AC, 4- Pole 5-Wire Grounding, Screw Terminals, Blue, Watertight

## Features

- Industrial Grade
- Female Connector Body
- 20A 3-Phase Wye 120/208V AC
- 4- Pole 5-Wire Grounding
- Screw Terminals

## Application

High Ampacity Connections

## General

Catalog Number	520C9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Connector
UPC	781786251762

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	3 Phase Y 120/208 V
Voltage Rating Description	3 Phase Y 120/208V

## Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets

[Specifications - 520C9W](#)

