



Straight Blade Devices, Specialty Receptacles, Display Case, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brushed Brass Plate

By Bryant
Catalog # 5236BOX



Straight Blade Devices, Specialty Receptacles, Display Case, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brushed Brass Plate, Single Pack

Features

- Display Case
- Receptacle and Plate
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Commercial/Industrial

General

Catalog Number	5236BOX
Color	Brass
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Floor Box Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Special Use
Style	Floor Box Assembly
Type	Single Receptacle
UPC	781786424005

Dimensions

Display Size Weight Standard Sized Product 1.4 lb

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-24](#) [Catalog Page Catalogs - Bryant Full Line Catalog](#) [Specifications - 5236BOX](#)