



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, Side Wired, 15A 125V, 5-15R, Brown, Single Pack

By Bryant
Catalog # 5242



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side
Wired, 15A 125V, 5-15R, Brown, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Side Wired
- 15A 125V

Application

Extra Heavy Duty Compact Industrial Specification Grade

General

Catalog Number	5242
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786624788

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Weight	0.2 lb
--------	--------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 5242](#)