



# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, Side Wired, 15A 125V, 5-15R, Gray, Single Pack

By Bryant  
Catalog # 5242GRY



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side  
Wired, 15A 125V, 5-15R, Gray, Single Pack

## Features

- Duplex
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Side Wired
- 15A 125V

## Application

Extra Heavy Duty Compact Industrial Specification Grade

## General

Catalog Number	5242GRY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786624795

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Weight	0.2 lb
--------	--------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 5242GRY](#)