



Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black, Single Pack

By Bryant
Catalog # 5261BLK



Straight Blade Devices, Receptacles, Single,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
125V, 5-15R, Black, Single Pack

Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 125V
- 5-15R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5261BLK
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786714663

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in

Weight	0.1 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

[Catalog Page - BRY A-9 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 5261BLK](#)