



## Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black

By Bryant  
Catalog # 5262BBLKWR



Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black

### Features

- Weather-resistance complies with national electrical code requirements
- Finder Groove Face
- Triple wipe contacts
- Compact design

### Application

Hubbell-Pro Extra Heavy Duty

### General

Catalog Number	5262BBLKWR
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Weather Resistant Duplex
UPC	781786670044

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Installation Manuals - WIRING\\_PD2504\\_INSTALLINST](#)  
[Specifications - 5262BBLKWR](#)