



## Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown

By Bryant  
Catalog # 5262BN



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A  
125V, 5-15R, Brown

### Features

- Slender/compact design
- Finder Groove Face
- Triple wipe contacts

### Application

Hubbell-Pro Extra Heavy Duty

### General

Color	Brown
Environmental Conditions	Indoor Dry unless protected by additional means
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	781786715110

### Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

### Certifications and Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant A-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Installation Manuals - WIRING\\_PD2504\\_INSTALLINST](#)  
[Literature - General Literature - Heavy Duty Specification](#)  
[Grade Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-5262BN-SPEC-EN | REV 5/2023