



Straight Blade Devices,
Receptacles, Duplex,
Commercial/Industrial Grade, 2-
Pole 3-Wire Grounding, 15A 125V,
5-15R, Red

By Bryant
Catalog # 5262BRED

Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
125V, 5-15R, Red



Application

Hubbell-Pro Extra Heavy Duty

General

Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry unless protected by additional means
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	781786715073

Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	3.28 in
Weight	0.25 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Installation Manuals - WIRING_PD2504_INSTALLINST](#)
[Literature - General Literature - Heavy Duty Specification Grade Receptacles](#)



A proud member of the Hubbell Family.