



# Straight Blade Devices, Equipment Base Devices - Clamp Type, Back Wiring, Female Nylon Cup, Industrial/Commercial, 15A 125V, 5-15P

By Bryant  
Catalog # [5279](#)



Straight Blade Devices, Equipment Base Devices - Clamp Type, Back Wiring, Female Nylon Cup, Industrial/Commercial, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, White, Single Pack

## Application

Commercial/Industrial

## General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Flanged Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Clamp Type
Type	Flanged Receptacle
UPC	781786659957

## Dimensions

Dimensions	1.84 in x 2.50 in x 1.31 in
Display Size	Standard Sized Product
Height	1.31 in
Length	1.84 in
Weight	0.1 lb
Width	2.50 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-5279-SPEC-EN | REV 5/2023