



Straight Blade Devices, Specialty Receptacles, Single, Commercial/Industrial Grade, 15A 125V, 5-15R, Mounted to 4" Round Cover

By Bryant
Catalog # 5281



Straight Blade Devices, Specialty Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack, Mounted to 4" Round Cover

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	Brown
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Specialty Receptacle
UPC	781786625211

Dimensions

Display Size	Standard Sized Product
Weight	0.25 lb

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Bryant A-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5281-SPEC-EN | REV 5/2023