



## Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled 12 Position, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, SinglePack

By Bryant  
Catalog # [5295](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled 12 Position, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, White, SinglePack

### Application

Heavy Duty

### General

Color	Black
Cord Range	0.300"-0.655"
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Extra Heavy Duty
Type	Plug
UPC	781786174108

### Dimensions

Display Size	Standard Sized
Length	1.25 in
Weight	0.2 lb
Width	2.07 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

### Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications and Compliance

Nema Rating	5-15P
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-5295-SPEC-EN | REV 5/2023