



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 30A 3-Phase Wye 120/208V AC, Watertight

By Bryant
Catalog # 530B9W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Screw Terminals, Blue, Watertight

Features

- Industrial Grade
- Male Flanged Inlet
- 30A 3-Phase Wye 120/208V AC
- 4- Pole 5-Wire Grounding
- Screw Terminals

Application

High Ampacity Watertight Connections

General

Catalog Number	530B9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C

Type	w/o impact
UPC	Inlet 781786251823

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	3 Phase Y 120/208 V
Voltage Rating Description	3 Phase Y 120/208V
Wattage	6240

Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Product Assets

[Specifications - 530B9W](#)