



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 30A 3-Phase Wye 277/480V AC, Watertight



By Bryant
Catalog # 530C7W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 30A 3-Phase Wye 277/480V AC, 4- Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

Features

- Industrial Grade
- Female Connector Body
- 30A 3-Phase Wye 277/480V AC
- 4- Pole 5-Wire Grounding
- Screw Terminals

Application

High Ampacity Connections

General

Catalog Number	530C7W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Connector
UPC	781786251830

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase Y 277/480 V
Voltage Rating Description	3 Phase Y 277/480V

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 530C7W](#)