



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 32A 220-415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

By Bryant
Catalog # 532P6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 32A 220-415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

Application

High Ampacity Connections

General

Color	Red
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Plugs
UPC	781786251915

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Multi Phase
Voltage Rating	200/346 V 240/415 V
Voltage Rating Description	200/346 V 240/415 V
Wattage	13280

Conductor Related

Cord Type	All Portable
Number Of Wires	5-Wire
Wire Size	#12 AWG to #8 AWG

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalog Page - Bryant K-5 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-532P6W-SPEC-EN | REV 5/2023