



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-415V, Screw Terminals, Watertight

By Bryant
Catalog # 532R6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

Features

- Industrial Grade
- Female Receptacle
- 32A 220-415V
- 4-Pole 5-Wire Grounding
- Screw Terminals

Application

High Ampacity Connections

General

Catalog Number	532R6W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786251922

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Three Phase
Voltage Rating	200/346 V 240/415 V
Voltage Rating Description	200/346V 240/415V
Wattage	13280

Conductor Related

Number Of Wires	5-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Product Assets

[Specifications - 532R6W](#)