



# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side Wired, 20A 125V, 5-20R, Brown, Single Pack

By Bryant  
Catalog # 5342



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side Wired, 20A 125V, 5-20R, Brown, Single Pack

## Application

Extra Heavy Duty Compact Industrial Specification Grade

## General

Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786625327

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	3.28 in
Weight	0.2 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRY-5342-SPEC-EN | REV 5/2024