



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, Side Wired, 20A 125V, 5-20R, Red, Single Pack

By Bryant
Catalog # [5342RED](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side
Wired, 20A 125V, 5-20R, Red, Single Pack

Application

Extra Heavy Duty Compact Industrial Specification Grade

General

Color	Red
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786714694

Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	3.28 in
Weight	0.2 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5342RED-SPEC-EN | REV 5/2023