



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, White

By Bryant
Catalog # [5352W](#)

Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, White



Features

- Slender/compact design
- Smooth face
- Triple wipe contacts

Application

Hubbell-Pro Extra Heavy Duty

General

Color	White
Environmental Conditions	Indoor Dry unless protected by additional means
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Smooth Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	783585530857

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5352W-SPEC-EN | REV 4/2023