



# Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack

By Bryant  
Catalog # 5361GRY



Straight Blade Devices, Receptacles, Single,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A  
125V, 5-20R, Gray, Single Pack

## Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 20A 125V
- 5-20R

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	5361GRY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786625433

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in

Weight	0.1 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-9](#) [Catalog Page  
Catalogs - Bryant Full Line Catalog  
Specifications - 5361GRY](#)