



Straight Blade Devices, Receptacles, Single, Weather Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Brown

By Bryant
Catalog # 5361WR



Straight Blade Devices, Receptacles, Single, Weather Resistant,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5- 20R, Brown, Single Pack

Features

- Single
- Weather Resistant
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 20A 125V

Application

Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|--------------------|
| Catalog Number | 5361WR |
| Color | Brown |
| EU RoHS Indicator | No |
| Environmental Conditions | Weather Resistant |
| Item Type | Single |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Extra Heavy Duty |
| Style | Finder Groove Face |
| Type | Single Receptacle |
| UPC | 781786670716 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.38 in x 0.91 in |
| Display Size | Standard Sized Product |
| Height | 0.91 in |

| | |
|--------|---------|
| Length | 3.28 in |
| Weight | 0.15 lb |
| Width | 1.38 in |

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 2500 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - BRY A-9 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 5361WR](#)