



**Straight Blade Devices,  
Receptacles, Single, Weather  
Resistant, Commercial/Industrial  
Grade, 2-Pole 3-Wire Grounding,  
20A 125V, 5- 20R, Single Pack**

By Bryant  
Catalog # 5361WWR



Straight Blade Devices, Receptacles, Single, Weather Resistant,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A  
125V, 5- 20R, White, Single Pack

**General**

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	5361WWR
Color	White
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786670761

**Dimensions**

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

**Electrical Ratings**

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

**Conductor Related**

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

**Certifications And Compliance**

Nema Rating	5-20R
-------------	-------

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

[Catalog Page - BRY A-9 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-5361WWR-SPEC-EN | REV 6/2024