



Straight Blade Devices,  
Receptacles, Single, Weather  
Resistant, Commercial/Industrial  
Grade, 2-Pole 3-Wire Grounding,  
20A 125V, 5- 20R, Single Pack

By Bryant  
Catalog # 5361WWR



Straight Blade Devices, Receptacles, Single, Weather Resistant,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A  
125V, 5- 20R, White, Single Pack

Features

- Single
- Weather Resistant
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 20A 125V

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5361WWR
Color	White
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786670761

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in

Length	3.28 in
Weight	0.15 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-9](#) [Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 5361WWR](#)



A Hubbell brand