



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, Gray

By Bryant
Catalog # 5362BGRY



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, Gray

Application

Hubbell-Pro Extra Heavy Duty

General

| | |
|------------------------------|-----------------------------------------------------|
| Catalog Number | 5362BGRY |
| Color | Gray |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry unless protected by additional means |
| Item Type | Traditional Duplex |
| Material | Thermoplastic/Composite |
| Material - Mounting Hardware | Screw Mounting |
| Mounting Type | Screw Mount |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Hubbell-PRO |
| Size | Standard Sized Product |
| Style | Finder Groove Face |
| Temperature Rating | Maximum continuous 75°C; minimum -40°C (w/o impact) |
| Type | Standard Duplex |
| UPC | 781786715035 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.38 in x 0.92 in |
| Display Size | Standard Sized Product |
| Height | 0.92 in |
| Length | 3.28 in |
| Weight | 0.25 lb |
| Width | 1.38 in |

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 1875 W |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #12 AWG to #10 AWG |

Certifications And Compliance

| | |
|----------------------|-----------------------------------------------------------------------------------------------------|
| Industry Standard(s) | UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant |
| Nema Rating | 5-20R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - BRY A-10 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Installation Manuals - WIRING_PD2504_INSTALLINST](#)
- [Literature - General Literature - Heavy Duty Specification Grade Receptacles](#)
- [Specifications - 5362BGRY](#)