



# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown

By Bryant  
Catalog # 5362BN



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A  
125V, 5-20R, Brown

## Application

Hubbell-Pro Extra Heavy Duty

## General

Catalog Number	5362BN
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry unless protected by additional means
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	781786715059

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	3.28 in
Weight	0.2 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-20R

## Logistics

Carton Quantity	10
Pallet Quantity	3600

## Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Installation Manuals - WIRING\\_PD2504\\_INSTALLINST](#)  
[Literature - General Literature - Heavy Duty Specification Grade Receptacles](#)  
[Specifications - 5362BN](#)