



# Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, White, Single Pack

By Bryant  
Catalog # 5378



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, White, Single Pack

## General

Application	Extra Heavy Duty Industrial
Catalog Number	5378
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Single Flanged
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Clamp Type
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786661301

## Dimensions

Dimensions	1.84 in x 2.50 in x 1.55 in
Display Size	Standard Sized Product
Height	1.55 in
Length	1.84 in
Weight	0.05 lb
Width	2.5 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY A-10 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY-5378-SPEC-EN | REV 6/2024