



Straight Blade Devices, Female Receptacles, Flanged, Industrial Grade, Nylon Cup, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack

By Bryant
Catalog # [5379](#)



Straight Blade Devices, Female Receptacles, Flanged, Industrial Grade, Nylon Cup, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack

Application

Commercial/Industrial

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Flanged Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Clamp Type
Type	Flanged Inlet
UPC	781786661356

Dimensions

Dimensions	1.84 in x 2.50 in x 1.31 in
Display Size	Standard Sized Product
Height	1.31 in
Length	1.84 in
Weight	0.05 lb
Width	2.50 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5379-SPEC-EN | REV 5/2023